

# SCE-1008SC Cut Sheet



Saginaw enclosure, NEMA 3R/4/12/13, 10 x 8 x 4in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-1008SC>

## Technical Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Brand</b>                        | Saginaw                      |
| <b>Item</b>                         | Enclosure                    |
| <b>Subpanel</b>                     | Purchase subpanel separately |
| <b>Slope Top</b>                    | No                           |
| <b>3-Piece Assembly</b>             | No                           |
| <b>Vented</b>                       | No                           |
| <b>NEMA Rating</b>                  | 3R/4/12/13                   |
| <b>IP Rating</b>                    | IP66                         |
| <b>Nominal Enclosure Dimensions</b> | 10 x 8 x 4in (HxWxD)         |
| <b>Enclosure Height</b>             | 10.44in                      |
| <b>Enclosure Width</b>              | 8.31in                       |
| <b>Enclosure Depth</b>              | 4.15in                       |

|                                 |              |
|---------------------------------|--------------|
| <b>Mounting</b>                 | Wall         |
| <b>Integral Mounting Feet</b>   | No           |
| <b>Integral Mounting Flange</b> | Yes          |
| <b>Dual Access</b>              | No           |
| <b>Knockouts</b>                | No           |
| <b>Bottom Gland Plate</b>       | No           |
| <b>Material</b>                 | Carbon steel |
| <b>Color</b>                    | ANSI 61 gray |
| <b>Finish</b>                   | Powder coat  |
| <b>Cover Type</b>               | Screw cover  |
| <b>Padlockable</b>              | No           |
| <b>Keylocking</b>               | No           |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | E69392  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |