

SCE-16K1608SSST Cut Sheet



Saginaw sanitary enclosure, slope top, NEMA 3R/4/4X/12, 16 x 16 x 8in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, single-door, 1/4-turn sanitary stainless steel latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-16K1608SSST>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Saginaw |
| Item | Sanitary enclosure |
| Subpanel | Purchase subpanel separately |
| Slope Top | Yes |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 3R/4/4X/12 |
| IP Rating | IP69K |
| Nominal Enclosure Dimensions | 16 x 16 x 8in (HxWxD) |
| Enclosure Height | 18.10in |
| Enclosure Width | 16.00in |
| Enclosure Depth | 9.10in |
| Mounting | Wall |
| Integral Mounting Feet | No |

| | |
|----------------------------------|---|
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | 304 stainless steel |
| Finish | #4 brush |
| Cover Type | Single-door |
| Hinge Type | Internal mount swing-out hinges |
| Number of Hinges Per Door | 2 |
| Latch Type | 1/4-turn sanitary stainless steel latch |
| Number Of Latches | 1 |
| Padlockable | No |
| Keylocking | No |
| Includes | (1) SCE-116398 key |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |