

SCE-20C30ELJSS Cut Sheet



Saginaw operator console, NEMA 3R/4/4X/12/13, 20 x 30 x 13in (HxWxD), desktop or pedestal mount, 304 stainless steel, #4 brush finish, single-door, 1/4-turn semi-flush latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-20C30ELJSS>

Technical Specifications

Brand	Saginaw	Dual Access	No
Item	Operator console	Knockouts	No
Subpanel	Purchase subpanel separately	Material	304 stainless steel
Slope Top	No	Finish	#4 brush
NEMA Rating	3R/4/4X/12/13	Cover Type	Single-door
IP Rating	IP66	Hinge Type	ELJ removable hinge
Nominal Enclosure Dimensions	20 x 30 x 13in (HxWxD)	Number of Hinges Per Door	2
Enclosure Height	17.84in	Number of Lid Hinges	2
Enclosure Width	24.00in	Latch Type	1/4-turn semi-flush latch
Enclosure Depth	13.09in	Number Of Latches	3
Mounting	Desktop or pedestal	Padlockable	No
Integral Mounting Feet	No	Keylocking	No
Integral Mounting Flange	No	Additional Information	Purchase pedestal column separately

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement