

SCE-20HMI2406SSLP Cut Sheet



Saginaw HMI Enclosure, NEMA 3R/4/4X/12/13, 20 x 24 x 6in (HxWxD), suspension or pedestal mount, dual access, 304 stainless steel, #4 brush finish, screw cover front, single door rear, 1/4-turn semi-flush latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-20HMI2406SSLP>

Technical Specifications

Brand	Saginaw
Item	HMI Enclosure
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	3R/4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	20 x 24 x 6in (HxWxD)
Enclosure Height	20.27in
Enclosure Width	24.27in
Enclosure Depth	7.25in
Mounting	Suspension or pedestal

Dual Access	Yes
Knockouts	No
Material	304 stainless steel
Finish	#4 brush
Cover Type	Screw cover front, single door rear
Hinge Type	Concealed hinges
Number of Hinges Per Door	2
Latch Type	1/4-turn semi-flush latch
Number Of Latches	1
Padlockable	No
Keylocking	No
Additional Information	Max front cut-out area 17.5 x 21.5in

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SCE-20HMI2406SSLP.pdf>
See store item page for other formats.