

SCE-30R2412LP Cut Sheet



Saginaw enclosure, NEMA 3R, 30 x 24 x 12in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 1/4-turn padlocking wing handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-30R2412LP>

Technical Specifications

Brand	Saginaw	Knockouts	No
Item	Enclosure	Bottom Gland Plate	No
Subpanel	Purchase subpanel separately	Material	Carbon steel
Slope Top	No	Color	ANSI 61 gray
3-Piece Assembly	No	Finish	Powder coat
Vented	No	Cover Type	Single-door
NEMA Rating	3R	Hinge Type	Concealed hinges
IP Rating	IP32	Number of Hinges Per Door	2
Nominal Enclosure Dimensions	30 x 24 x 12in (HxWxD)	Latch Type	1/4-turn padlocking wing handle
Enclosure Height	30.00in	Number Of Latches	1
Enclosure Width	24.20in	Secondary Latch Type	1/4-turn semi-flush
Enclosure Depth	13.70in	Number Of Secondary Latches	1
Mounting	Wall	Shelf	No
Integral Mounting Feet	No	Padlockable	Yes
Integral Mounting Flange	No	Keylocking	No
Dual Access	No		

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-30R2412LP.pdf>
See store item page for other formats.