

SCE-5PB Cut Sheet



Saginaw pushbutton enclosure, 5 holes, 30mm, NEMA 4/12/13, 13 x 4 x 3in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-5PB>

Technical Specifications

Brand	Saginaw	Enclosure Depth	2.91in
Item	Pushbutton enclosure	Mounting	Wall
Number of Pushbutton Holes	5 holes	Integral Mounting Feet	No
Pushbutton Hole Nominal Size	30mm	Integral Mounting Flange	Yes
Slope Top	No	Dual Access	No
NEMA Rating	4/12/13	Knockouts	No
IP Rating	IP66	Material	Carbon steel
Nominal Enclosure Dimensions	13 x 4 x 3in (HxWxD)	Color	ANSI 61 gray
Enclosure Height	12.81in	Finish	Powder coat
Enclosure Width	3.56in	Cover Type	Screw cover
		Padlockable	No
		Keylocking	No

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-5PB.pdf>
See store item page for other formats.