

SCE-66CCOLSS Cut Sheet



Saginaw straight pedestal column, 304 stainless steel, 35.00 x 6.00 x 6.00in, #4 brush finish. For use with operator consoles. Flange gaskets, box connector and mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-66CCOLSS>

Technical Specifications

Brand	Saginaw
Item	Straight pedestal column
Material	304 stainless steel
Size	35.00 x 6.00 x 6.00in
Finish	#4 brush
NEMA Rating	4/4X/12/13
For Use With	Operator consoles
Includes	Flange gaskets, box connector and mounting hardware
Additional Information	Purchase column base separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-66CCOLSS.pdf>
See store item page for other formats.