

SCE-AC5100B230VSS6 Cut Sheet



Saginaw Enviro-Therm air conditioner, 5100 BTU/H, R-134a, 230 VAC operating voltage, 316 stainless steel housing, side mount. For use with NEMA/UL Type 3R, 4, 4X & 12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-AC5100B230VSS6>

Technical Specifications

Brand	Saginaw
Series	Enviro-Therm
Item	Air conditioner
Nominal Cooling Capacity	5100 BTU/H
Operating Voltage	230 VAC
Frequency	50/60 Hz
Running Current	7.1A
Refrigerant	R-134a
Height	45.28in
Width	15.55in
Depth	10.63in

Mounting	Side
Filter-Free	No
Filter Size	14.88 x 11.81in
Housing Material	316 stainless steel
IP Rating	IP56
For Use With	NEMA/UL Type 3R, 4, 4X & 12 enclosures
Includes	Washable/reusable filter, mounting template, and hardware
Dangerous Goods	<ul style="list-style-type: none">• Packaging Instructions: 200• UN Number: 3159• Hazard Type: Compressed Gas

Agency Approvals

UL Listed File #	E498756
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SCE-AC5100B230VSS6.pdf>
See store item page for other formats.