

SCE-EXR12-30T200 Cut Sheet



Saginaw add-on rotary disconnect enclosure, NEMA 3R/12/13, door, 24 x 17 x 12in (HxWxD), external mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 1/4-turn semi-flush, galvanized subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-EXR12-30T200>

Technical Specifications

Brand	Saginaw
Item	Add-on rotary disconnect enclosure
Slope Top	No
Vented	No
NEMA Rating	3R/12/13
IP Rating	IP66
Disconnect Mounting	Door
Nominal Enclosure Dimensions	24 x 17 x 12in (HxWxD)
Enclosure Height	24.00in
Enclosure Width	17.00in
Enclosure Depth	12.00in
Mounting	External
Integral Mounting Feet	No

Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	2
Latch Type	1/4-turn semi-flush
Padlockable	No
Keylocking	No
Subpanel	Galvanized subpanel included
Includes	Cable-operated mechanical interlock and mounting hardware

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-EXR12-30T200.pdf>
See store item page for other formats.