

SCE-L9308ELJSS Cut Sheet



Saginaw wiring trough, 8 x 9 x 30in (HxDxL), NEMA 3R/4/4X/12/13, wall mount, 304 stainless steel, #4 brush finish, single-door.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-L9308ELJSS>

Technical Specifications

Brand	Saginaw
Item	Wiring trough
Series	Enviroline Junction
NEMA Rating	3R/4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	9 x 30 x 8in (HxWxD)
Enclosure Height	9.00in
Enclosure Depth	8.18in
Enclosure Length	30.00in

Mounting	Wall
Integral Mounting Feet	No
Knockouts	No
Material	304 stainless steel
Finish	#4 brush
Cover Type	Single-door
Latch Type	1/4-turn semi-flush latch
Padlockable	No

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-L9308ELJSS.pdf>
See store item page for other formats.