

SCE-N86C7818 Cut Sheet



Saginaw NextGen series center enclosure bay, NEMA 3R/4/12/13, 86 x 78 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, polyester powder coat finish, 2-door, 3-point padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-N86C7818>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Saginaw |
| Item | Enclosure bay |
| Series | NextGen |
| Subpanel | Purchase subpanel separately |
| Bay Type | Center |
| Slope Top | No |
| NEMA Rating | 3R/4/12/13 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 86 x 78 x 18in (HxWxD) |
| Enclosure Height | 86.00in |
| Enclosure Width | 77.75in |
| Enclosure Depth | 18.00in |
| Mounting | Freestanding |
| Integral Mounting Feet | No |
| Integral Mounting Flange | No |

| | |
|----------------------------------|---------------------------------|
| Dual Access | No |
| Knockouts | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Polyester powder coat |
| Cover Type | 2-door |
| Hinge Type | Concealed hinges |
| Number of Hinges Per Door | 4 |
| Latch Type | 3-point padlocking combo handle |
| Number Of Latches | 1 |
| Shelf | No |
| Padlockable | Yes |
| Keylocking | No |
| Includes | Gasket and hardware for baying |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SCE-N86C7818.pdf>
See store item page for other formats.