

SCE-NEP8024SS Cut Sheet



Saginaw NextGen series side exterior panel, 80 x 24in (HxD), 304 stainless steel, #4 brush finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-NEP8024SS>

Technical Specifications

Brand	Saginaw
Series	NextGen
Item	Side exterior panel
Height	79in
Depth	23.5in
Material	304 stainless steel
Finish	#4 brush
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SCE-NEP8024SS.pdf>
See store item page for other formats.