


# SCE-SK156068SS Cut Sheet

Saginaw skirt kit, 14.94 x 59.75in, 304 stainless steel, #4 brush finish. For use with 60-68in wide floor-mount enclosures on 15in floor stands.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-SK156068SS>



## Technical Specifications

<b>Brand</b>	Saginaw
<b>Item</b>	Skirt kit
<b>Height</b>	14.94in
<b>Width</b>	59.75in
<b>Material</b>	304 stainless steel
<b>Finish</b>	#4 brush
<b>Vented</b>	No
<b>For Use With</b>	60-68in wide floor-mount enclosures on 15in floor stands
<b>Kit Includes</b>	(2) skirt panels and mounting hardware

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-SK156068SS.pdf>  
See store item page for other formats.