

SCU-2502 Cut Sheet



ProSense signal conditioner, isolated, frequency input, relay output, 21.6-253 VAC/19.2-300 VDC operating voltage, 35mm DIN rail mount, removable screw terminal plugs.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCU-2502>

Technical Specifications

Brand	ProSense
Item	Signal conditioner
Isolation	Isolated
Field Configurable	Yes
Input Frequency Signal Range	0.001 Hz-100 kHz
Relay Configuration	(2) Form A (SPST) relays
Load Current	230 VAC 2A/24 VDC 1A maximum
Operating Voltage	21.6-253 VAC/19.2-300 VDC
Housing Material	Plastic
Mounting	35mm DIN rail
Electrical Connection	Removable screw terminal plugs
Requires	SCU-PDM2 for programming, sold separately

Agency Approvals

UL Listed File #	E197592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SCU-2502.pdf>
See store item page for other formats.