

# SDN12202108PL Cut Sheet



Wiegmann disconnect enclosure, NEMA 12/13, right flange, 20 x 21 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 2-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SDN12202108PL>

## Technical Specifications

<b>Brand</b>	Wiegmann	<b>Integral Mounting Feet</b>	Yes
<b>Item</b>	Disconnect enclosure	<b>Material</b>	Carbon steel
<b>Slope Top</b>	No	<b>Color</b>	ANSI 61 gray
<b>Vented</b>	No	<b>Finish</b>	Powder coat
<b>NEMA Rating</b>	12/13	<b>Cover Type</b>	Single-door
<b>Disconnect Mounting</b>	Right flange	<b>Hinge Type</b>	Continuous hinge
<b>Nominal Enclosure Dimensions</b>	20 x 21 x 8in (HxWxD)	<b>Number of Hinges Per Door</b>	1
<b>Enclosure Height</b>	20.00in	<b>Latch Type</b>	2-point padlocking handle
<b>Enclosure Width</b>	21.38in	<b>Padlockable</b>	Yes
<b>Enclosure Depth</b>	8.88in	<b>Keylocking</b>	No
<b>Mounting</b>	Wall	<b>Subpanel</b>	Purchase subpanel separately

## Agency Approvals

<b>UL Listed File #</b>	E64791
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SDN12202108PL.pdf>  
See store item page for other formats.