

# SDN12202110PL Cut Sheet



Wiegmann disconnect enclosure, NEMA 12/13, right flange, 20 x 21 x 10in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 2-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SDN12202110PL>

## Technical Specifications

|                                 |                      |
|---------------------------------|----------------------|
| <b>Brand</b>                    | Wiegmann             |
| <b>Item</b>                     | Disconnect enclosure |
| <b>Slope Top</b>                | No                   |
| <b>NEMA Rating</b>              | 12/13                |
| <b>Disconnect Mounting</b>      | Right flange         |
| <b>Nominal Enclosure Height</b> | 20in                 |
| <b>Nominal Enclosure Width</b>  | 21.38in              |
| <b>Nominal Enclosure Depth</b>  | 10.88in              |
| <b>Mounting</b>                 | Wall                 |
| <b>Integral Mounting Feet</b>   | Yes                  |
| <b>Material</b>                 | Carbon steel         |
| <b>Color</b>                    | ANSI 61 gray         |

|                                  |                                                                                                                   |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------|
| <b>Finish</b>                    | Powder coat                                                                                                       |
| <b>Cover Type</b>                | Single-door                                                                                                       |
| <b>Hinge Type</b>                | Continuous hinge                                                                                                  |
| <b>Number of Hinges Per Door</b> | 1                                                                                                                 |
| <b>Latch Type</b>                | 2-point padlocking handle                                                                                         |
| <b>Padlockable</b>               | Yes                                                                                                               |
| <b>Keylocking</b>                | No                                                                                                                |
| <b>Subpanel</b>                  | Purchase subpanel separately                                                                                      |
| <b>Additional Information</b>    | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

## Agency Approvals

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>UL Listed File #</b>     | E64791                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SDN12202110PL.pdf>  
See store item page for other formats.