

# SDN12363212PL Cut Sheet



Wiegmann disconnect enclosure, NEMA 12/13, right flange, 36 x 31 x 12in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 2-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SDN12363212PL>

## Technical Specifications

Brand	Wiegmann
Item	Disconnect enclosure
Slope Top	No
Vented	No
NEMA Rating	12/13
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	36 x 31 x 12in (HxWxD)
Enclosure Height	36.00in
Enclosure Width	31.37in
Enclosure Depth	12.88in
Mounting	Wall

Integral Mounting Feet	Yes
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	2-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Purchase subpanel separately

## Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SDN12363212PL.pdf>  
See store item page for other formats.