


SE-SW8MG-4P Cut Sheet



STRIDE industrial Layer 2 managed Ethernet switch, 8 ports, (8) Ethernet Gigabit (RJ45) and (4) SFP combo Gigabit port(s), EtherNet/IP and Modbus TCP, -40 to +75 deg C, metal housing, IP40, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE-SW8MG-4P>

Technical Specifications

Brand	STRIDE
Item	Ethernet switch
Grade	Industrial
Switch Type	Layer 2 managed
Number of Ports	8
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (8) Ethernet Gigabit (RJ45)• (4) SFP combo Gigabit
Port Protocol(s)	<ul style="list-style-type: none">• Modbus TCP• webserver (secure HTTPS)

Port Speed(s)	10/100/1000 Mbps auto-detect
Operating Temperature	-40 to +75 deg C
Housing Material	Metal
IP Rating	IP40
Mounting	35mm DIN rail
Additional Information	Optional SFP modules sold separately
Application	Hazardous location rated

Agency Approvals

UL Listed File #	E200031
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SE-SW8MG-4P.pdf>
See store item page for other formats.