

# SE2-SW8U Cut Sheet



STRIDE industrial unmanaged Ethernet switch, 8 ports, (8) Ethernet 10/100Base-T (RJ45) port(s), -10 to +60 deg C, metal housing, IP30, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE2-SW8U>

## Technical Specifications

<b>Brand</b>	STRIDE
<b>Item</b>	Ethernet switch
<b>Grade</b>	Industrial
<b>Switch Type</b>	Unmanaged
<b>Number of Ports</b>	8
<b>Communication Port and Connection Type(s)</b>	(8) Ethernet 10/100Base-T (RJ45)
<b>Port Speed(s)</b>	10/100 Mbps auto-detect
<b>Operating Temperature</b>	-10 to +60 deg C
<b>Housing Material</b>	Metal
<b>IP Rating</b>	IP30
<b>Mounting</b>	35mm DIN rail
<b>Application</b>	Hazardous location rated

## Agency Approvals

<b>UL Listed File #</b>	E200031
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	E200031
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>