

SE3-IJ2B2UG-T Cut Sheet



STRIDE industrial unmanaged, PoE++ injector, IEEE 802.3af/at/bt, up to 90W, 2 ports, (1) PoE++ Gigabit (RJ45) and (1) Ethernet Gigabit (RJ45) port(s), 9-55 VDC nominal input, -40 to +75 deg C, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE3-IJ2B2UG-T>

Technical Specifications

Brand	STRIDE
Item	PoE++ injector
Grade	Industrial
Switch Type	Unmanaged
PoE Standard	IEEE 802.3af/at/bt
Maximum PoE Output Power	60W @ 9 VDC, 90W @ 12-55 VDC
Maximum PoE Output Power per Port	90W
Number of Ports	2
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (1) PoE++ Gigabit (RJ45)• (1) Ethernet Gigabit (RJ45)
Port Speed(s)	10/100/1000 Mbps auto-detect

Nominal Input Voltage	9-55 VDC
Number of Output Points	1
Nominal Output Voltage	24 VDC
Relay Configuration	(1) Form A (SPST) relay
Number of Isolated Commons	1
Load Current	1A/point
Operating Temperature	-40 to +75 deg C
Housing Material	Metal
IP Rating	IP30
Mounting	35mm DIN rail or panel
Additional Information	Redundant power input design, 9-55 VDC

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SE3-IJ2B2UG-T.pdf>
See store item page for other formats.