

SE3-SW5U-1C1-T Cut Sheet



STRIDE industrial unmanaged Ethernet switch, 5 ports, (4) Ethernet 10/100Base-T (RJ45) and (1) multi-mode SC 100FX fiber port(s), -40 to +75 deg C, metal housing, IP30, NEMA TS2, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE3-SW5U-1C1-T>

Technical Specifications

Brand	STRIDE
Item	Ethernet switch
Grade	Industrial
Switch Type	Unmanaged
Number of Ports	5
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (4) Ethernet 10/100Base-T (RJ45)• (1) multi-mode SC 100FX fiber
Port Speed(s)	<ul style="list-style-type: none">• 10/100 Mbps auto-detect• 100 Mbps fiber
Nominal Input Voltage	12-48 VDC
Number of Output Points	1
Nominal Output Voltage	24 VDC
Relay Configuration	(1) Form A (SPST) relay

Number of Isolated Commons	1
Number of Points per Common	1
Load Current	1A/point
Operating Temperature	-40 to +75 deg C
Housing Material	Metal
IP Rating	IP30
NEMA Rating	TS2
Mounting	35mm DIN rail or panel
Application	Hazardous location rated

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	ANSI/ISA 12.12.01
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SE3-SW5U-1C1-T.pdf>
See store item page for other formats.