

SE3-SW5U-N67-T Cut Sheet



STRIDE industrial unmanaged Ethernet switch, 5 ports, (5) Ethernet 10/100Base-T (M12) port(s), -40 to +75 deg C, plastic housing, IP67, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE3-SW5U-N67-T>

Technical Specifications

| | |
|---|---------------------------------|
| Brand | STRIDE |
| Item | Ethernet switch |
| Grade | Industrial |
| Switch Type | Unmanaged |
| Number of Ports | 5 |
| Communication Port and Connection Type(s) | (5) Ethernet 10/100Base-T (M12) |
| Port Speed(s) | 10/100 Mbps auto-detect |
| Nominal Input Voltage | 12-48 VDC |
| Operating Temperature | -40 to +75 deg C |
| Housing Material | Plastic |
| IP Rating | IP67 |
| Mounting | 35mm DIN rail or panel |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E157382 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SE3-SW5U-N67-T.pdf>
See store item page for other formats.