

SE3-SW8U-N67-T Cut Sheet



STRIDE industrial unmanaged Ethernet switch, 8 ports, (8) Ethernet 10/100Base-T (4-pin M12 D-coded female) port(s), -40 to +75 °C, plastic housing, IP67, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE3-SW8U-N67-T>

Technical Specifications

Brand	STRIDE
Item	Ethernet switch
Grade	Industrial
Switch Type	Unmanaged
Number of Ports	8
Communication Port and Connection Type(s)	(8) Ethernet 10/100Base-T (4-pin M12 D-coded female)
Communication Standard(s)	<ul style="list-style-type: none">• IEEE 802.3 10Base-T• IEEE 802.3u 100Base-TX/FX• IEEE 802.3x Flow Control

Port Speed(s)	10/100 Mbps auto-detect
Redundant Input Power	No
Nominal Input Voltage	24 VDC
Operating Temperature	-40 to +75 °C
Housing Material	Plastic
IP Rating	IP67
Mounting	35mm DIN rail or panel

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SE3-SW8U-N67-T.pdf>
See store item page for other formats.