

SEP1-SW5U-T Cut Sheet



STRIDE PRO industrial unmanaged+ Ethernet switch, 5 ports, (5) Ethernet 10/100Base-T (RJ45) port(s), -40 to +75 °C, metal housing, IP30, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEP1-SW5U-T>

Technical Specifications

Brand	STRIDE PRO
Item	Ethernet switch
Grade	Industrial
Switch Type	Unmanaged+
Number of Ports	5
Communication Port and Connection Type(s)	(5) Ethernet 10/100Base-T (RJ45)
Communication Standard(s)	<ul style="list-style-type: none">• IEEE 802.3 10Base-T• IEEE 802.3u 100Base-TX/FX• IEEE 802.3x Flow Control• IEEE 802.1D Broadcast Storm Protection (BSP)
Port Speed(s)	10/100 Mbps auto-detect
Redundant Input Power	Yes
Nominal Input Voltage	12-48 VDC

Number of Output Points	1
Nominal Output Voltage	24 VDC
Relay Configuration	(1) Form A (SPST) relay
Number of Isolated Commons	1
Number of Points per Common	1
Load Current	1A/point
Operating Temperature	-40 to +75 °C
Housing Material	Metal
IP Rating	IP30
Mounting	35mm DIN rail or panel
Additional Information	Port prioritization

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SEP1-SW5U-T.pdf>
See store item page for other formats.