

SF-1002-BR-H Cut Sheet



CITO StackFlow modular manual valve, 2-way, 2-position, glass-filled nylon body, stackable, Cv=21.3. FT-200 temperature gauge and RA-3903 high-flow turbine included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SF-1002-BR-H>

Technical Specifications

Brand	CITO
Item	Valve
Working Fluid	Coolant, oil or water
Valve Type	Manual process
Series	StackFlow
Port Quantity	2-way
Number Of Positions	2
Body Material	Glass-filled nylon
Stackable	Yes
Flow Coefficient	21.3
Maximum Operating Pressure	100 psi
Minimum Operating Pressure	0 psi
Working Fluid Temperature	20 to 160 deg F
Form Factor	Modular
Includes	FT-200 temperature gauge and RA-3903 high-flow turbine

Agency Approvals

CE	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SF-1002-BR-H.pdf>
See store item page for other formats.