

SHR-43C-22-22 Cut Sheet



Sung-II Machinery drive coupling, servo high gain, aluminum alloy, clamp, size 43, 22 x 22mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SHR-43C-22-22>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Servo high gain
Material	Aluminum alloy
Rated Torque	16 N-m
Maximum Torque	32 N-m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	0.2mm

Maximum RPM	14000
Attachment Style	Clamp
Coupling Size	43
Bore Diameter	22mm
Bore Diameter 2	22mm
Outside Diameter	42.8mm
Clamp Screw Fastening Torque	3.7 N-m
Clamp Screw Size	M4

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SHR-43C-22-22.pdf>
See store item page for other formats.