

# SJC-20C-8 Cut Sheet



Sung-II Machinery drive coupling hub, jaw type, aluminum alloy, clamp, size 20, 8mm bore. Requires SJC-20 series spiders.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SJC-20C-8>

## Technical Specifications

|                                     |                    |
|-------------------------------------|--------------------|
| <b>Brand</b>                        | Sung-II Machinery  |
| <b>Item</b>                         | Drive coupling hub |
| <b>Coupling Type</b>                | Jaw type           |
| <b>Material</b>                     | Aluminum alloy     |
| <b>Maximum Angular Misalignment</b> | 1.0 degrees        |
| <b>Maximum RPM</b>                  | 15000              |
| <b>Attachment Style</b>             | Clamp              |

|                                     |                       |
|-------------------------------------|-----------------------|
| <b>Coupling Size</b>                | 20                    |
| <b>Bore Diameter</b>                | 8mm                   |
| <b>Outside Diameter</b>             | 20mm                  |
| <b>Clamp Screw Fastening Torque</b> | 1N-m                  |
| <b>Clamp Screw Size</b>             | M2.6                  |
| <b>Requires</b>                     | SJC-20 series spiders |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | None  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | RoHS Statement  |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SJC-20C-8.pdf>  
See store item page for other formats.