

SJC-55C-19.05 Cut Sheet



Sung-II Machinery drive coupling hub, jaw type, aluminum alloy, clamp, size 55, 3/4in bore. Requires SJC-55 series spiders.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SJC-55C-19.05>

Technical Specifications

| | |
|-------------------------------------|-----------------------|
| Brand | Sung-II Machinery |
| Item | Drive coupling hub |
| Coupling Type | Jaw type |
| Material | Aluminum alloy |
| Maximum Angular Misalignment | 1.0 degrees |
| Maximum RPM | 6500 |
| Attachment Style | Clamp |
| Coupling Size | 55 |
| Bore Diameter | 3/4in |
| Outside Diameter | 55mm |
| Clamp Screw Fastening Torque | 13N-m |
| Clamp Screw Size | M6 |
| Requires | SJC-55 series spiders |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |