

# SJC-65C-19 Cut Sheet



Sung-II Machinery drive coupling hub, jaw type, aluminum alloy, clamp, size 65, 19mm bore. Requires SJC-65 series spiders.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SJC-65C-19>

## Technical Specifications

<b>Brand</b>	Sung-II Machinery
<b>Item</b>	Drive coupling hub
<b>Coupling Type</b>	Jaw type
<b>Material</b>	Aluminum alloy
<b>Maximum Angular Misalignment</b>	1.0 degrees
<b>Maximum RPM</b>	5500
<b>Attachment Style</b>	Clamp

<b>Coupling Size</b>	65
<b>Bore Diameter</b>	19mm
<b>Outside Diameter</b>	65mm
<b>Clamp Screw Fastening Torque</b>	30N-m
<b>Clamp Screw Size</b>	M8
<b>Requires</b>	SJC-65 series spiders

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	RoHS Statement

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SJC-65C-19.pdf>  
See store item page for other formats.