

SLS-SA3-08 Cut Sheet



Datalogic safety laser scanner, area protection, 275 degrees operating angle, 0.05 - 3m operating distance, (1) safety zone, (2) warning zones, 24 VDC, safety category Type 3, IP65, (1) 4-pin and (1) 8-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SLS-SA3-08>

Technical Specifications

Brand	Datalogic
Item	Safety laser scanner
Series	Sentinel
Function	Area protection
Operating Angle	275 degrees
Angular Resolution	0.1 degree
Operating Distance	0.05 - 3m
Operating Zones	(1) safety zone, (2) warning zones

Configurable	Yes
Input Voltage	24 VDC
Switching Output	(2) OSSD outputs
Safety Category	Type 3
Light Curtain Features	Muting and restart capability
IP Rating	IP65
Connection	(1) 4-pin and (1) 8-pin M12 quick-disconnect
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E481590
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SLS-SA3-08.pdf>
See store item page for other formats.