

SMPO-3B Cut Sheet



ReeR safety light curtain, sender/receiver pair, body protection, 24 VDC, 400mm resolution, 810mm protected height, 0-12m operating distance, safety category Type 4, configurable, IP65 IP67, (6) 5-pin and (1) 12-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SMPO-3B>

Technical Specifications

Brand	ReeR
Series	Safegate
Item	Safety light curtain
Light Curtain Type	Sender/receiver pair
Function	Body protection
Input Voltage	24 VDC
Beam Resolution	400mm
Protected Height	810mm
Operating Distance	0-12m

Safety Category	Type 4
Switching Output	(2) OSSD outputs
Connection	(6) 5-pin and (1) 12-pin M12 quick-disconnect
IP Rating	IP65 IP67
Configurable	Yes
Light Curtain Features	Muting, partial muting, external device monitoring and restart capability
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E193188
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SMPO-3B.pdf>
See store item page for other formats.