

SOH-20C-6.35 Cut Sheet



Sung-II Machinery drive coupling hub, Oldham, aluminum alloy, clamp, size 20, 1/4in bore. Requires SOH-20-DISC torque disc.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOH-20C-6.35>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling hub
Coupling Type	Oldham
Material	Aluminum alloy
Rated Torque	1.5 N-m
Maximum Torque	3 N-m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	1.5mm

Maximum RPM	11000
Attachment Style	Clamp
Coupling Size	20
Bore Diameter	1/4in
Outside Diameter	20mm
Clamp Screw Fastening Torque	1 N-m
Clamp Screw Size	M2.6
Requires	SOH-20-DISC torque disc

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SOH-20C-6.35.pdf>
See store item page for other formats.