

SOHM-70C-28.575 Cut Sheet



Sung-II Machinery drive coupling hub, Oldham, aluminum alloy, clamp, size 70, 1-1/8in bore. Requires SOH-70-DISC torque disc.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOHM-70C-28.575>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling hub
Coupling Type	Oldham
Material	Aluminum alloy
Rated Torque	60 N-m
Maximum Torque	120 N-m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	3.5mm

Maximum RPM	4500
Attachment Style	Clamp
Coupling Size	70
Bore Diameter	1-1/8in
Outside Diameter	73mm
Clamp Screw Fastening Torque	30 N-m
Clamp Screw Size	M8
Requires	SOH-70-DISC torque disc

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SOHM-70C-28.575.pdf>
See store item page for other formats.