

# SR35-AUX-IO Cut Sheet



Stellar SR35 series temperature combo module, thermistor, 1-channel input, 2-point input, 110-230 VAC/24 VDC, 2-point output, 250 VAC, (2) Form A (SPST) relays. For use with Stellar SR35 series soft starters. (1) 500mm ribbon cable included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SR35-AUX-IO>

## Technical Specifications

<b>Brand</b>	Stellar
<b>Item</b>	Combo module
<b>I/O Module Type</b>	Temperature
<b>Input Signal Type(s)</b>	Thermistor
<b>Series</b>	SR35
<b>Number Of Input Channels</b>	1
<b>Input Thermistor Signal Types</b>	4K (PTC)
<b>Number of Input Points</b>	2
<b>Nominal Input Voltage</b>	110-230 VAC/24 VDC
<b>Discrete Input Type</b>	Sinking
<b>Number of Output Points</b>	2
<b>Nominal Output Voltage</b>	250 VAC
<b>Discrete Output Type</b>	Relay
<b>Relay Configuration</b>	(2) Form A (SPST) relays
<b>Load Current</b>	0.75A/point
<b>Number of Isolated Discrete Output Commons</b>	2
<b>Number of Points per Discrete Output Common</b>	1
<b>For Use With</b>	Stellar SR35 series soft starters
<b>Includes</b>	(1) 500mm ribbon cable

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>