

SR55-CM-ENETIP2 Cut Sheet



Stellar SR55 series communication module, EtherNet/IP, 2 ports, (2) Ethernet (RJ45 full duplex) port(s). For use with Stellar SR55 series soft starters.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SR55-CM-ENETIP2>

Technical Specifications

Brand	Stellar
Item	Communication module
Series	SR55
Number of Ports	2
Communication Port and Connection Type(s)	(2) Ethernet (RJ45 full duplex)
Port Protocol(s)	<ul style="list-style-type: none">• EtherNet/IP adapter• EtherNet/IP implicit messaging• EtherNet/IP explicit messaging• TCP/IP• CIP• transformer isolated interface
Port Speed(s)	10/100 Mbps
For Use With	Stellar SR55 series soft starters

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SR55-CM-ENETIP2.pdf>
See store item page for other formats.