

SRB-22C-6.35-6.35 Cut Sheet



Sung-II Machinery drive coupling, servo-beam, 7075-T6 aluminum alloy, clamp, size 22, 6.35 (1/4in) x 6.35mm (1/4in) bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SRB-22C-6.35-6.35>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Servo-beam
Material	7075-T6 aluminum alloy
Rated Torque	1 N-m
Maximum Torque	2 N-m
Maximum Angular Misalignment	2.5 degrees
Maximum Parallel Misalignment	0.15mm
Maximum RPM	18000
Attachment Style	Clamp
Coupling Size	22
Bore Diameter	1/4in
Bore Diameter 2	1/4in
Outside Diameter	22.2mm
Clamp Screw Fastening Torque	1.7 N-m
Clamp Screw Size	M3

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement