

SRB-22C-9.525-10 Cut Sheet



Sung-II Machinery drive coupling, servo-beam, 7075-T6 aluminum alloy, clamp, size 22, 9.525 (3/8in) x 10mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SRB-22C-9.525-10>

Technical Specifications

| | |
|--------------------------------------|------------------------|
| Brand | Sung-II Machinery |
| Item | Drive coupling |
| Coupling Type | Servo-beam |
| Material | 7075-T6 aluminum alloy |
| Rated Torque | 1 N-m |
| Maximum Torque | 2 N-m |
| Maximum Angular Misalignment | 2.5 degrees |
| Maximum Parallel Misalignment | 0.15mm |

| | |
|-------------------------------------|---------|
| Maximum RPM | 18000 |
| Attachment Style | Clamp |
| Coupling Size | 22 |
| Bore Diameter | 3/8in |
| Bore Diameter 2 | 10mm |
| Outside Diameter | 22.2mm |
| Clamp Screw Fastening Torque | 1.7 N-m |
| Clamp Screw Size | M3 |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SRB-22C-9.525-10.pdf>
See store item page for other formats.