

SRB-26C-6-6.35 Cut Sheet



Sung-II Machinery drive coupling, servo-beam, 7075-T6 aluminum alloy, clamp, size 26, 6 x 6.35mm (1/4in) bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SRB-26C-6-6.35>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Servo-beam
Material	7075-T6 aluminum alloy
Rated Torque	2 N-m
Maximum Torque	4 N-m
Maximum Angular Misalignment	2.5 degrees
Maximum Parallel Misalignment	0.2mm
Maximum RPM	17000
Attachment Style	Clamp
Coupling Size	26
Bore Diameter	6mm
Bore Diameter 2	1/4in
Outside Diameter	26.2mm
Clamp Screw Fastening Torque	1.7 N-m
Clamp Screw Size	M3

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement