

SRB-E-301ST-CC Cut Sheet



Schmersal safety relay, configurable, 2-channel, 24 VAC/VDC, 12 configurations, (3) N.O. safety output(s), (1) N.C. monitoring output(s), push-in cage clamp.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SRB-E-301ST-CC>

Technical Specifications

Brand	Schmersal
Item	Safety relay
Relay Type	Configurable
Number Of Channels	2
Control Voltage	24 VAC/VDC
Restart Type	Manual or automatic restart
Number Of Configurations	12 configurations
Configuration Types	<ul style="list-style-type: none">• cross-wire monitoring = yes/no• input sensor = NC/NC or NC/NO• synchronous monitoring = yes/no• safety mat evaluation

Safety Input Type	(1) pair digital
Safety Output Type	(3) N.O.
Monitoring Output Type	(1) N.C.
Connection	Push-in cage clamp

Agency Approvals

UL Listed File #	E57648
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SRB-E-301ST-CC.pdf>
See store item page for other formats.