

SRB-E-322ST-CC Cut Sheet



Schmersal safety relay, configurable, release delay, 0 to 30 seconds, 2-channel, 24 VDC, 10 configurations, (3) delayed N.O. and (2) OSSD safety output(s), (1) N.C and (1) status monitoring output(s), push-in cage clamp.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SRB-E-322ST-CC>

Technical Specifications

Brand	Schmersal
Item	Safety relay
Relay Type	Configurable
Delay Type	Release delay
Monitoring Circuit	0 to 30 seconds
Number Of Channels	2
Control Voltage	24 VDC
Restart Type	Manual or automatic restart

Number Of Configurations	10 configurations
Configuration Types	<ul style="list-style-type: none">• cross-wire monitoring = yes/no• input sensor = NC/NC or NC/NO• synchronous monitoring = yes/no
Safety Input Type	(1) pair digital
Safety Output Type	(3) delayed N.O. and (2) OSSD
Monitoring Output Type	(1) N.C and (1) status
Connection	Push-in cage clamp

Agency Approvals

UL Listed File #	E57648
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SRB-E-322ST-CC.pdf>
See store item page for other formats.