

SRBA-32C-8-8 Cut Sheet



Sung-II Machinery drive coupling, servo-beam, 7075-T6 aluminum alloy, clamp, size 32, 8 x 8mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SRBA-32C-8-8>

Technical Specifications

| | |
|--------------------------------------|------------------------|
| Brand | Sung-II Machinery |
| Item | Drive coupling |
| Coupling Type | Servo-beam |
| Material | 7075-T6 aluminum alloy |
| Rated Torque | 3.8 N-m |
| Maximum Torque | 7.6 N-m |
| Maximum Angular Misalignment | 2.5 degrees |
| Maximum Parallel Misalignment | 0.2mm |

| | |
|-------------------------------------|---------|
| Maximum RPM | 14000 |
| Attachment Style | Clamp |
| Coupling Size | 32 |
| Bore Diameter | 8mm |
| Bore Diameter 2 | 8mm |
| Outside Diameter | 31.8mm |
| Clamp Screw Fastening Torque | 3.5 N-m |
| Clamp Screw Size | M4 |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SRBA-32C-8-8.pdf>
See store item page for other formats.