

SRBA-32C-9.525-10 Cut Sheet



Sung-II Machinery drive coupling, servo-beam, 7075-T6 aluminum alloy, clamp, size 32, 9.525 (3/8in) x 10mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SRBA-32C-9.525-10>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Servo-beam
Material	7075-T6 aluminum alloy
Rated Torque	3.8 N-m
Maximum Torque	7.6 N-m
Maximum Angular Misalignment	2.5 degrees
Maximum Parallel Misalignment	0.2mm
Maximum RPM	14000
Attachment Style	Clamp
Coupling Size	32
Bore Diameter	3/8in
Bore Diameter 2	10mm
Outside Diameter	31.8mm
Clamp Screw Fastening Torque	3.5 N-m
Clamp Screw Size	M4

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement