

SSN43024123PT Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12/13, 30 x 24 x 12in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, single-door, 3-point 316L padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SSN43024123PT>

Technical Specifications

Brand	Wiegmann	Integral Mounting Flange	No
Item	Enclosure	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	304 stainless steel
Vented	No	Finish	No. 3 intermediate polished
NEMA Rating	4/4X/12/13	Cover Type	Single-door
Nominal Enclosure Dimensions	30 x 24 x 12in (HxWxD)	Hinge Type	Stainless steel continuous hinge
Enclosure Height	30.00in	Number of Hinges Per Door	1
Enclosure Width	24.00in	Latch Type	3-point 316L padlocking handle
Enclosure Depth	13.03in	Shelf	No
Mounting	Wall	Padlockable	Yes
Integral Mounting Feet	Yes	Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SSN43024123PT.pdf>
See store item page for other formats.