

# SSN4302416A Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12/13, 30 x 24 x 16in (HxWxD), wall mount, 316L stainless steel, No. 3 intermediate polished finish, single-door, (7) stainless steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SSN4302416A>

## Technical Specifications

|                          |                              |
|--------------------------|------------------------------|
| Brand                    | Wiegmann                     |
| Item                     | Enclosure                    |
| Subpanel                 | Purchase subpanel separately |
| Slope Top                | No                           |
| NEMA Rating              | 4/4X/12/13                   |
| IP Rating                | IP66                         |
| Nominal Enclosure Height | 30in                         |
| Nominal Enclosure Width  | 24in                         |
| Nominal Enclosure Depth  | 16in                         |
| Mounting                 | Wall                         |
| Integral Mounting Feet   | Yes                          |
| Integral Mounting Flange | No                           |

|                           |                                  |
|---------------------------|----------------------------------|
| Dual Access               | No                               |
| Knockouts                 | No                               |
| Material                  | 316L stainless steel             |
| Finish                    | No. 3 intermediate polished      |
| Cover Type                | Single-door                      |
| Hinge Type                | Stainless steel continuous hinge |
| Number of Hinges Per Door | 1                                |
| Latch Type                | (7) stainless steel clamps       |
| Padlock Attachment Type   | Padlock hasp and staple          |
| Padlockable               | Yes                              |
| Keylocking                | No                               |

## Agency Approvals

|                      |                                        |
|----------------------|----------------------------------------|
| UL Listed File #     | E64791                                 |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SSN4302416A.pdf>  
See store item page for other formats.