

SSN4306010WF3PT Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12, 30 x 60 x 10in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, 2-door, 3-point 316L padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SSN4306010WF3PT>

Technical Specifications

| | |
|---------------------------------|------------------------------|
| Brand | Wiegmann |
| Item | Enclosure |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| NEMA Rating | 4/4X/12 |
| Nominal Enclosure Height | 30in |
| Nominal Enclosure Width | 60in |
| Nominal Enclosure Depth | 10in |
| Mounting | Wall |
| Integral Mounting Feet | Yes |
| Integral Mounting Flange | No |

| | |
|----------------------------------|----------------------------------|
| Dual Access | No |
| Knockouts | No |
| Material | 304 stainless steel |
| Finish | No. 3 intermediate polished |
| Cover Type | 2-door |
| Hinge Type | Stainless steel continuous hinge |
| Number of Hinges Per Door | 1 |
| Latch Type | 3-point 316L padlocking handle |
| Padlockable | Yes |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64791 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SSN4306010WF3PT.pdf>
See store item page for other formats.