

SSN4363010 Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12/13, 36 x 30 x 10in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, single-door, (7) stainless steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SSN4363010>

Technical Specifications

| | | | |
|-------------------------------------|------------------------------|----------------------------------|----------------------------------|
| Brand | Wiegmann | Integral Mounting Flange | No |
| Item | Enclosure | Dual Access | No |
| Subpanel | Purchase subpanel separately | Knockouts | No |
| Slope Top | No | Bottom Gland Plate | No |
| 3-Piece Assembly | No | Material | 304 stainless steel |
| Vented | No | Finish | No. 3 intermediate polished |
| NEMA Rating | 4/4X/12/13 | Cover Type | Single-door |
| IP Rating | IP66 | Hinge Type | Stainless steel continuous hinge |
| Nominal Enclosure Dimensions | 36 x 30 x 10in (HxWxD) | Number of Hinges Per Door | 1 |
| Enclosure Height | 36.00in | Latch Type | (7) stainless steel clamps |
| Enclosure Width | 30.00in | Padlock Attachment Type | Padlock hasp and staple |
| Enclosure Depth | 11.03in | Shelf | No |
| Mounting | Wall | Padlockable | Yes |
| Integral Mounting Feet | Yes | Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64791 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SSN4363010.pdf>
See store item page for other formats.