

# SSN4X242508 Cut Sheet



Wiegmann disconnect enclosure, NEMA 4/4X/12/13, right flange, 24 x 25 x 8in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, single-door, (7) stainless steel clamps, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SSN4X242508>

## Technical Specifications

|                          |                      |
|--------------------------|----------------------|
| Brand                    | Wiegmann             |
| Item                     | Disconnect enclosure |
| Slope Top                | No                   |
| NEMA Rating              | 4/4X/12/13           |
| Disconnect Mounting      | Right flange         |
| Nominal Enclosure Height | 24in                 |
| Nominal Enclosure Width  | 25.38in              |
| Nominal Enclosure Depth  | 8.97in               |
| Mounting                 | Wall                 |
| Integral Mounting Feet   | Yes                  |
| Material                 | 304 stainless steel  |

|                           |                                                                                                                   |
|---------------------------|-------------------------------------------------------------------------------------------------------------------|
| Finish                    | No. 3 intermediate polished                                                                                       |
| Cover Type                | Single-door                                                                                                       |
| Hinge Type                | Stainless steel continuous hinge                                                                                  |
| Number of Hinges Per Door | 1                                                                                                                 |
| Latch Type                | (7) stainless steel clamps                                                                                        |
| Padlockable               | No                                                                                                                |
| Keylocking                | No                                                                                                                |
| Subpanel                  | Purchase subpanel separately                                                                                      |
| Additional Information    | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

## Agency Approvals

|                      |                                        |
|----------------------|----------------------------------------|
| UL Listed File #     | E64791                                 |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SSN4X242508.pdf>  
See store item page for other formats.