

ST12126LG Cut Sheet



Hammond Eclipse series enclosure, slope top, NEMA 3R/4/12, 12 x 12 x 6in (HxWxD), wall mount, carbon steel, RAL 7035 light gray, powder coat finish, single-door, 1/4-turn semi-flush latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ST12126LG>

Technical Specifications

Brand	Hammond	Integral Mounting Flange	No
Item	Enclosure	Dual Access	No
Series	Eclipse	Knockouts	No
Subpanel	Purchase subpanel separately	Material	Carbon steel
Slope Top	Yes	Color	RAL 7035 light gray
NEMA Rating	3R/4/12	Finish	Powder coat
IP Rating	IP66	Cover Type	Single-door
Nominal Enclosure Dimensions	12 x 12 x 6in (HxWxD)	Hinge Type	Concealed hinges
Enclosure Height	14.18in	Number of Hinges Per Door	2
Enclosure Width	12.00in	Latch Type	1/4-turn semi-flush latch
Enclosure Depth	6.82in	Number Of Latches	1
Mounting	Wall	Padlockable	No
Integral Mounting Feet	No	Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document