

# STP-MTRAC-23078 Cut Sheet



SureStep stepper motor, NEMA 23 frame, IP40, single shaft, 0.71A, 227 oz-in holding torque, 1.8-degree step angle, 200 steps per revolution, bipolar.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/STP-MTRAC-23078>

## Technical Specifications

<b>Brand</b>	SureStep	<b>Shaft Diameter</b>	1/4in
<b>Item</b>	Stepper motor	<b>Amperage Rating</b>	0.71A
<b>Voltage Type</b>	DC	<b>Holding Torque Rating</b>	227 oz-in
<b>Motor Type</b>	Brushless	<b>Step Angle</b>	1.8-degree
<b>Number of Output Phases</b>	2	<b>Steps per Revolution</b>	200
<b>Integrated Brake</b>	No	<b>Winding Type</b>	Bipolar
<b>Motor Frame</b>	NEMA 23	<b>Cable Length</b>	10ft
<b>IP Rating</b>	IP40	<b>Connector Type</b>	Pigtail
<b>Shaft Type</b>	Single	<b>Additional Information</b>	Optimized for AC-input stepper drives

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/STP-MTRAC-23078.pdf>  
See store item page for other formats.