

# STP-PWR-4805 Cut Sheet



SureStep unregulated linear power supply, 48 VDC @ 5A/240W and 5 VDC @ 0.5A/2.5W, 120/240 VAC nominal input, 1-phase, open frame, aluminum housing, chassis mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/STP-PWR-4805>

## Technical Specifications

Brand	SureStep	Protection Type(s)	fused overcurrent
Item	Power supply	Remote On/Off	No
Power Supply Type	Unregulated linear	Voltage Monitoring	No
Efficiency	89%	Enclosure Type	Open frame
Output Configuration	Dual output	Housing Material	Aluminum
Output	48 VDC @ 5A/240W	Mounting	Chassis
Output 2	5 VDC @ 0.5A/2.5W	Connector Type	Screw terminals
Output Voltage Range	48 VDC at 5A unregulated, 5 VDC at 0.5A regulated	NEC Class 2	No
Input voltage range	120/240 VAC	Integrated UPS Battery Control	No
Input Voltage Selection Type	Switch	Operating Temperature	0 to 70 deg C
Number of Input Phases	1		

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E181899
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/STP-PWR-4805.pdf>  
See store item page for other formats.